

Grooved pin, full length parallel with chamfer DIN 1473 Free-cutting steel 4X14MM



Article number	39730.040.014
Brand	-
UBB	500645371575
UNSPSC	31163215
EAN	8717077084247
PKG. of 100	Full Box Only

Technical Parameters

d ₁	4
Diameter (mm)	4
Length (L) (mm)	14
Info	<p>V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d# is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.</p>
Material	Free-cutting steel

Standards

ISO	8740
DIN	1473

Technical Specification

c ≈	0.4
d ₂ ≈	4.25
f ≈	1.8

Technical Drawing

$r \approx 4$

Tolerance h11

UR COURSE
10.6

SETTING THE STANDARD
IN FASTENING SOLUTIONS

