



Grooved pin, full length parallel with chamfer DIN 1473 Free-cutting steel 4X40MM

Article number	39730.040.040
Brand	-
UBB	950359660764
UNSPSC	31163215
EAN	8715492826138
PKG. of 100	Full Box Only

Technical Parameters

Diameter	4 mm
Length	40 mm
Material	Free-cutting steel
Info	V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Standards

DIN	1473
ISO	≈8740
NEN	≈2604

Technical Specification

c ≈	0.4
d1	4
d2 ≈	4.25
D (mm)	4

Technical Drawing

$f \approx$	1.8
$L \text{ (mm)}$	40
$r \approx$	4
Tolerance	h11
V	10.6

