



Slotted countersunk head screw DIN 963 Brass CU2/ CU3 M3X10

Article number	48170.030.010
Brand	-
UBB	950353201342
UNSPSC	31161504
EAN	8715492848734
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	10 mm
Driving features	Slotted
Head shape	Countersunk head
Material	Brass
Material technical	CU2/CU3
Thread	Metric thread

Standards

NEN	≈2370
ASME	≈B18.6.7M
BS	≈4183
NF	≈E25-123
ISO	≈2009
DIN	963

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	10
n	0.8
P	0.5
t (min.)	0.6

Technical Drawing

