



Split pin (cotter pin) DIN 94
Copper 3,2X63MM

Article number	50390.032.063
Brand	-
UBB	950359164023
UNSPSC	31163204
EAN	8715492247018
PKG. of 250	Full Box Only

Technical Parameters

Diameter	3.2 mm
Length	63 mm
Material	Copper
Info	The shape of the split pin ends are at the manufacturer's discretion.For stainless steel split pins the type of austenitic stainless steel is at the manufacturer's discretion and may vary from the steel types stated in ISO 3506.The recommended tolerance class for the accommodating hole diameter d (nominal) is H13 for $d \leq 1,2$ mm and H14 for bigger diameters.The tolerance class of the nominal length (L) is js17.

Standards

DIN	94
ISO	1234
NF	E25-774
NEN	182

Technical Specification

a (max.)	3.2
b \approx	6.4

Technical Drawing

c (max.)	5.8
c (min.)	5.1
d (min.)	2.7
D (mm)	3.2
L (mm)	63
d (max.)	2.9

