

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Stainless Steel A2-70 M8X90

Article number	51000.080.090
Brand	-
UBB	950351763798
UNSPSC	31161620
EAN	8715492250476
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	90 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NEN	1555
ASME	B18.2.3.1M
ISO	4014
NF	E25-112
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	90
P	1.25
s	13

Technical Drawing

