

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Stainless Steel A2-70 M8X270

Article number	51000.080.270
Brand	-
UBB	500633212724
UNSPSC	31161620
EAN	8715494604772
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M8
Length	270 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Info Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ASME	B18.2.3.1M
NEN	1555
ISO	4014
DIN	931
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	270
P	1.25
s	13

Technical Drawing

