

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Stainless Steel A2-70 M12X180

Article number	51000.120.180
Brand	-
UBB	951351757194
UNSPSC	31161620
EAN	8715492251015
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M12
Length	180 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Info Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

DIN	931
NF	E25-112
ISO	4014
NEN	1555
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	180
P	1.75

Technical Drawing



