

DIN 933 Fully Threaded Metric Hexagon Head Bolt, Stainless Steel A2-70 M33X100

Article number	51010.330.100
Brand	-
UBB	951351796614
UNSPSC	31161620
EAN	8715492257499
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M33
Length	100 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ASME	B18.2.3.1M
DIN	933
ISO	4017
NF	E25-114
NEN	1568

Technical Specification

d-D	M33
k	21
L (mm)	100
P	3.5
s	50

Technical Drawing

