



**Hexagon socket
countersunk head screw
ISO 10642 Stainless steel A2
M3X5**

Article number	51060.030.005
Brand	-
UBB	500633170237
UNSPSC	31161518
EAN	8715494611220
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M3
Length	5 mm
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Info	All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class
------	--

Standards

ISO	10642
-----	-------

mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Technical Specification

b (min.)	18
d-D	M3
dk (max.)	5.81
Full thread if $L \leq$	25
k (max.)	1.86
L (mm)	5
P	0.5
s	2
α	90

Technical Drawing

