



Hexagon socket countersunk head screw ISO 10642 Stainless steel A2 M10X140

Article number	51060.100.140
Brand	-
UBB	500571272557
UNSPSC	31161518
EAN	8715494132060
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	140 mm
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Info	All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class
------	--

Standards

ISO	10642
-----	-------

mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Technical Specification

b (min.)	32
d-D	M10
dk (max.)	20.69
Full thread if $L \leq$	50
k (max.)	6.2
L (mm)	140
P	1.5
s	6
α	90

Technical Drawing

