



**Hexagon socket
countersunk head screw
ISO 10642 Stainless steel A2
M16X55**

Article number	51060.160.055
Brand	-
UBB	500633173611
UNSPSC	31161518
EAN	8715494611572
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	55 mm
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Info	All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class
------	--

Standards

ISO	10642
-----	-------

mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Technical Specification

b (min.)	48
d-D	M16
dk (max.)	30.61
Full thread if $L \leq$	70
k (max.)	8.8
L (mm)	55
P	2
s	10
α	90

Technical Drawing

