



Hexagon thin nut DIN 439 2 Stainless steel A2 035 M22

Article number	51090.220.001
Brand	-
UBB	950355562329
UNSPSC	31161727
EAN	8715492268099
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M22
Class	035
Driving features	Hexagon
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Standards

DIN	439-2
ASME	B18.2.4.5M
NF	E25-405-1
ISO	4035
NEN	2334-B

Technical Specification

d-D	M22
m	11
P	2.5
s	32

Technical Drawing

