



Slotted countersunk head screw DIN 963 Stainless steel A2 70 M1,4X12

Article number	51110.014.012
Brand	-
UBB	500633180053
UNSPSC	31161504
EAN	8715494612210
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M1.4
Length	12 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	≈E25-123
NEN	≈2370
BS	≈4183
ISO	≈2009
DIN	963
ASME	≈B18.6.7M

Technical Specification

d-D	M1.4
Thread length (min.)	16
dk (max.)	2.6
Full thread if $L \leq$	16
k (max.)	0.84
L (mm)	12
n	0.3
P	0.3
t (min.)	0.28

Technical Drawing

