



Slotted countersunk head screw DIN 963 Stainless steel A2 70 M2X18

Article number	51110.020.018
Brand	-
UBB	500633180541
UNSPSC	31161504
EAN	8715494612265
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M2
Length	18 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	≈E25-123
DIN	963
ISO	≈2009
BS	≈4183
ASME	≈B18.6.7M
NEN	≈2370

Technical Specification

d-D	M2
Thread length (min.)	16
dk (max.)	3.8
Full thread if $L \leq$	18
k (max.)	1.2
L (mm)	18
n	0.5
P	0.4
t (min.)	0.4

Technical Drawing

