



Slotted countersunk head screw DIN 963 Stainless steel A2 70 M3X40

Article number	51110.030.040
Brand	-
UBB	950353247485
UNSPSC	31161504
EAN	8715492269270
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	40 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ASME	≈B18.6.7M
BS	≈4183
NF	≈E25-123
DIN	963
ISO	≈2009
NEN	≈2370

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	40
n	0.8
P	0.5
t (min.)	0.6

Technical Drawing

