



Slotted cheese head screw DIN 84 Stainless steel A2 70 M1X2

Article number	51120.010.002
Brand	-
UBB	500571320737
UNSPSC	31161504
EAN	8715494118965
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M1
Length	2 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NEN	≈1602
DIN	84
ASME	≈B18.6.7M
ISO	≈1207
NF	≈E25-127
BS	≈4183

Technical Specification

d-D	M1
Thread length (min.)	25
dk (max.)	2
Full thread if L ≤	30
k (max.)	0.7
L (mm)	2
n	0.25
P	0.25
t (min.)	0.25

Technical Drawing