



Slotted cheese head screw DIN 84 Stainless steel A2 70 M1,4X10

Article number	51120.014.010
Brand	-
UBB	500571321230
UNSPSC	31161504
EAN	8715494119016
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M1.4
Length	10 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	≈E25-127
BS	≈4183
NEN	≈1602
ASME	≈B18.6.7M
DIN	84
ISO	≈1207

Technical Specification

d-D	M1.4
Thread length (min.)	25
dk (max.)	2.6
Full thread if L ≤	30
k (max.)	0.9
L (mm)	10
n	0.3
P	0.3
t (min.)	0.4

Technical Drawing