



Slotted cheese head screw DIN 84 Stainless steel A2 70 M4X90

Article number	51120.040.090
Brand	-
UBB	950353461391
UNSPSC	31161504
EAN	8715492271594
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	90 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

BS	≈4183
ASME	≈B18.6.7M
ISO	≈1207
NF	≈E25-127
NEN	≈1602
DIN	84

Technical Specification

d-D	M4
Thread length (min.)	38
dk (max.)	7
Full thread if L ≤	40
k (max.)	2.6
L (mm)	90
n	1.2
P	0.7
t (min.)	1.1

Technical Drawing