



Slotted cheese head screw DIN 84 Stainless steel A2 M8X70

Article number	51120.080.070
Brand	-
UBB	950353264613
UNSPSC	31161504
EAN	8715492272157
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	70 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NEN	≈1602
ASME	≈B18.6.7M
ISO	≈1207
NF	≈E25-127
DIN	84
BS	≈4183

Technical Specification

d-D	M8
Thread length (min.)	38
dk (max.)	13
Full thread if L ≤	40
k (max.)	5
L (mm)	70
n	2
P	1.25
t (min.)	2

Technical Drawing