



Hexagon socket set screw with dog point DIN 915 Stainless steel A2 M6X20

Article number	51230.060.020
Brand	-
UBB	952351511490
UNSPSC	31161518
EAN	8715492276278
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	20 mm
Driving features	Hexagon socket
Material	Stainless steel
Material technical	A2
Thread direction	Right
Point	Dog
Thread	Metric thread
Info	These set screws are designed for pressure loads and are not suitable for tensile- or shear loads.

Standards

DIN	915
BS	4168-4
NEN	2344
ISO	4028
ASME	B18.3.6M
NF	E27-182

Technical Specification

d-D	M6
dp (max.)	4
L (mm)	20
P	1
s	3
t (min.)	2
z long (min.)	3
z long if L ≥	10
z short (min.)	1.5

Technical Drawing

