



Hexagon socket set screw with dog point DIN 915 Stainless steel A2 M6X40

Article number	51230.060.040
Brand	-
UBB	500571475192
UNSPSC	31161518
EAN	8715494114042
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	40 mm
Driving features	Hexagon socket
Material	Stainless steel
Material technical	A2
Thread direction	Right
Point	Dog
Thread	Metric thread
Info	These set screws are designed for pressure loads and are not suitable for tensile- or shear loads.

Standards

ISO	4028
BS	4168-4
NF	E27-182
DIN	915
NEN	2344
ASME	B18.3.6M

Technical Specification

d-D	M6
dp (max.)	4
L (mm)	40
P	1
s	3
t (min.)	2
z long (min.)	3
z long if L ≥	10
z short (min.)	1.5

Technical Drawing

