



Hexagon socket set screw with dog point DIN 915 Stainless steel A2 M10X35

Article number	51230.100.035
Brand	-
UBB	500571476182
UNSPSC	31161518
EAN	8715494114141
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M10
Length	35 mm
Driving features	Hexagon socket
Material	Stainless steel
Material technical	A2
Thread direction	Right
Point	Dog
Thread	Metric thread
Info	These set screws are designed for pressure loads and are not suitable for tensile- or shear loads.

Standards

DIN	915
BS	4168-4
ISO	4028
ASME	B18.3.6M
NF	E27-182
NEN	2344

Technical Specification

d-D	M10
dp (max.)	7
L (mm)	35
P	1.5
s	5
t (min.)	4
z long (min.)	5
z long if L ≥	16
z short (min.)	2.5

Technical Drawing

