



Hexagon socket set screw with dog point DIN 915 Stainless steel A2 M16X20

Article number	51230.160.020
Brand	-
UBB	500571477586
UNSPSC	31161518
EAN	8715494114288
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M16
Length	20 mm
Driving features	Hexagon socket
Material	Stainless steel
Material technical	A2
Thread direction	Right
Point	Dog
Thread	Metric thread
Info	These set screws are designed for pressure loads and are not suitable for tensile- or shear loads.

Standards

NF	E27-182
ISO	4028
DIN	915
NEN	2344
BS	4168-4
ASME	B18.3.6M

Technical Specification

d-D	M16
dp (max.)	12
L (mm)	20
P	2
s	8
t (min.)	6.4
z long (min.)	8
z long if L ≥	25
z short (min.)	4

Technical Drawing

