



## Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M1,6X3

|                |               |
|----------------|---------------|
| Article number | 51300.016.003 |
| Brand          | -             |
| UBB            | 500571329902  |
| UNSPSC         | 31161504      |
| EAN            | 8715494115384 |
| PKG. of 1000   | Full Box Only |

### Technical Parameters

|                    |                  |
|--------------------|------------------|
| Diameter           | M1.6             |
| Length             | 3 mm             |
| Class              | 70               |
| Driving features   | Phillips         |
| Head shape         | Countersunk head |
| Material           | Stainless steel  |
| Material technical | A2               |
| Thread             | Metric thread    |

### Standards

|     |            |
|-----|------------|
| ISO | ≈7046-1    |
| DIN | 965        |
| NF  | ≈E25-119-1 |

### Technical Specification

|                         |      |
|-------------------------|------|
| d-D                     | M1.6 |
| Thread length (min.)    | 15   |
| dk (max.)               | 3    |
| Full thread if $L \leq$ | 16   |
| k (max.)                | 0.96 |
| L (mm)                  | 3    |
| No. cross recess        | 0    |
| P                       | 0.35 |

### Technical Drawing

