



## Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M2X6

|                |               |
|----------------|---------------|
| Article number | 51300.020.006 |
| Brand          | -             |
| UBB            | 950353275197  |
| UNSPSC         | 31161504      |
| EAN            | 8715492281043 |
| PKG. of 100    | Full Box Only |

### Technical Parameters

|                    |                  |
|--------------------|------------------|
| Diameter           | M2               |
| Length             | 6 mm             |
| Class              | 70               |
| Driving features   | Phillips         |
| Head shape         | Countersunk head |
| Material           | Stainless steel  |
| Material technical | A2               |
| Thread             | Metric thread    |

### Standards

|     |            |
|-----|------------|
| ISO | ≈7046-1    |
| NF  | ≈E25-119-1 |
| DIN | 965        |

### Technical Specification

|                         |     |
|-------------------------|-----|
| d-D                     | M2  |
| Thread length (min.)    | 16  |
| dk (max.)               | 3.8 |
| Full thread if $L \leq$ | 18  |
| k (max.)                | 1.2 |
| L (mm)                  | 6   |
| No. cross recess        | 1   |
| P                       | 0.4 |

### Technical Drawing

