



## Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M2X8

Article number	51300.020.008
Brand	-
UBB	950353275270
UNSPSC	31161504
EAN	8715492281050
PKG. of 100	Full Box Only

### Technical Parameters

Diameter (d-D)	M2
Length (L) (mm)	8
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

### Standards

NF	E25-119-2
ISO	7046-2-H
DIN	965 A-H

### Technical Specification

Thread length (min.)	16
$d_k$ (max.)	3.8
Full thread if $L \leq$	18
k (max.)	1.2
No. cross recess	1
P	0.40

### Technical Drawing

