



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M3X18

Article number	51300.030.018
Brand	-
UBB	500571330975
UNSPSC	31161504
EAN	8715494115483
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	18 mm
Class	70
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ISO	≈7046-1
NF	≈E25-119-1
DIN	965

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	18
No. cross recess	1
P	0.5

Technical Drawing

