



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M4X6

Article number	51300.040.006
Brand	-
UBB	950353550318
UNSPSC	31161504
EAN	8715492281296
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	6 mm
Class	70
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	≈E25-119-1
DIN	965
ISO	≈7046-1

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	6
No. cross recess	2
P	0.7

Technical Drawing

