



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M4X40

Article number	51300.040.040
Brand	-
UBB	950353550805
UNSPSC	31161504
EAN	8715492281395
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	40 mm
Class	70
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ISO	≈7046-1
NF	≈E25-119-1
DIN	965

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	40
No. cross recess	2
P	0.7

Technical Drawing

