

## Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M5X60



Article number	51300.050.060
Brand	-
UBB	950353551894
UNSPSC	31161504
EAN	8715492281548
PKG. of 100	Full Box Only

### Technical Parameters

Diameter (d-D)	M5
Length (L) (mm)	60
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

### Standards

ISO	7046-2-H
DIN	965 A-H
NF	E25-119-2

### Technical Specification

Thread length (min.)	25
$d_k$ (max.)	9.2
Full thread if $L \leq$	30
$k$ (max.)	2.5
No. cross recess	2
P	0.80

### Technical Drawing

