

## Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M6X55



Article number	51300.060.055
Brand	-
UBB	500571332203
UNSPSC	31161504
EAN	8715494115612
PKG. of 200	Full Box Only

### Technical Parameters

Diameter (d-D)	M6
Length (L) (mm)	55
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

### Standards

ISO	7046-2-H
NF	E25-119-2
DIN	965 A-H

### Technical Specification

Thread length (min.)	28
$d_k$ (max.)	11
Full thread if $L \leq$	35
k (max.)	3
No. cross recess	3
P	1

### Technical Drawing

