



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M10X70

Article number	51300.100.070
Brand	-
UBB	500571334100
UNSPSC	31161504
EAN	8715494115803
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	70 mm
Class	70
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	965
NF	≈E25-119-1
ISO	≈7046-1

Technical Specification

d-D	M10
Thread length (min.)	40
dk (max.)	18
Full thread if L ≤	50
k (max.)	5
L (mm)	70
No. cross recess	4
P	1.5

Technical Drawing

