



Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A2 M1,6X5

Article number	51302.016.005
Brand	-
UBB	951353116522
UNSPSC	31161504
EAN	8715492281852
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M1.6
Length	5 mm
Class	70
Driving features	Pozidriv
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ISO	≈7046-1
NF	≈E25-119-1
DIN	965

Technical Specification

d-D	M1.6
Thread length (min.)	15
dk (max.)	3
Full thread if $L \leq$	16
k (max.)	0.96
L (mm)	5
No. cross recess	0
P	0.35

Technical Drawing

