



Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A2 M2X10

Article number	51302.020.010
Brand	-
UBB	951353117512
UNSPSC	31161504
EAN	8715492281951
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M2
Length	10 mm
Class	70
Driving features	Pozidriv
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ISO	≈7046-1
DIN	965
NF	≈E25-119-1

Technical Specification

d-D	M2
Thread length (min.)	16
dk (max.)	3.8
Full thread if $L \leq$	18
k (max.)	1.2
L (mm)	10
No. cross recess	1
P	0.4

Technical Drawing

