



Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A2 M2X14

Article number	51302.020.014
Brand	-
UBB	951353117777
UNSPSC	31161504
EAN	8715492281975
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M2
Length	14 mm
Class	70
Driving features	Pozidriv
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	≈E25-119-1
DIN	965
ISO	≈7046-1

Technical Specification

d-D	M2
Thread length (min.)	16
dk (max.)	3.8
Full thread if $L \leq$	18
k (max.)	1.2
L (mm)	14
No. cross recess	1
P	0.4

Technical Drawing

