



Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A2 M5X8

Article number	51302.050.008
Brand	-
UBB	951353121225
UNSPSC	31161504
EAN	8715492282330
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M5
Length	8 mm
Class	70
Driving features	Pozidriv
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ISO	≈7046-1
NF	≈E25-119-1
DIN	965

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if $L \leq$	30
k (max.)	2.5
L (mm)	8
No. cross recess	2
P	0.8

Technical Drawing

