



Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A2 M5X14

Article number	51302.050.014
Brand	-
UBB	500571536993
UNSPSC	31161504
EAN	8715494123211
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	14 mm
Class	70
Driving features	Pozidriv
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	965
ISO	≈7046-1
NF	≈E25-119-1

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if $L \leq$	30
k (max.)	2.5
L (mm)	14
No. cross recess	2
P	0.8

Technical Drawing

