

Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A2 M5X16



Article number	51302.050.016
Brand	-
UBB	950353719541
UNSPSC	31161504
EAN	8715492282361
PKG. of 100	Full Box Only

Technical Parameters

Diameter (d-D)	M5
Length (L) (mm)	16
Driving features	Pozidriv
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	E25-119-2
DIN	965 A-Z
ISO	7046-2-Z

Technical Specification

Thread length (min.)	25
d_k (max.)	9.2
Full thread if $L \leq$	30
k (max.)	2.5
No. cross recess	2
P	0.80

Technical Drawing

