



Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A2 M5X20

Article number	51302.050.020
Brand	-
UBB	951353121555
UNSPSC	31161504
EAN	8715492282378
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M5
Length	20 mm
Class	70
Driving features	Pozidriv
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	≈E25-119-1
DIN	965
ISO	≈7046-1

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if L ≤	30
k (max.)	2.5
L (mm)	20
No. cross recess	2
P	0.8

Technical Drawing

