



Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A2 M6X16

Article number	51302.060.016
Brand	-
UBB	951353122470
UNSPSC	31161504
EAN	8715492282477
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M6
Length	16 mm
Class	70
Driving features	Pozidriv
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ISO	≈7046-1
DIN	965
NF	≈E25-119-1

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if L ≤	35
k (max.)	3
L (mm)	16
No. cross recess	3
P	1

Technical Drawing

