



Cross recessed raised countersunk head screw Phillips DIN 966 A-H Stainless steel A2 M2X30

Artikelnummer	51320.020.030
Merk	-
UBB	500633231203
UNSPSC	31161504
EAN	8715494592048
PKG. van 1000	Alleen volledige verpakkingen

Technische parameters

Diameter	M2
Length	30 mm
Class	70
Driving features	Phillips
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standaarden

DIN	966
ISO	≈7047
NF	≈E25-120

Technische specificatie

d-D	M2
Thread length (min.)	16
dk (max.)	3.8
f ≈	0.5
Full thread if L ≤	18
k (max.)	1.2
L (mm)	30
No. cross recess	1
P	0.4

Technische tekening

