



Cross recessed raised countersunk head screw Phillips DIN 966 A-H Stainless steel A2 M3X5

Article number	51320.030.005
Brand	-
UBB	500571410827
UNSPSC	31161504
EAN	8715494121347
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M3
Length	5 mm
Class	70
Driving features	Phillips
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ISO	≈7047
NF	≈E25-120
DIN	966

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
f ≈	0.75
Full thread if L ≤	22
k (max.)	1.65
L (mm)	5
No. cross recess	1
P	0.5

Technical Drawing

