

## Cross recessed raised cheese head screw Phillips DIN 7985-H Stainless steel A2 M1,6X8

|                |               |
|----------------|---------------|
| Article number | 51340.016.008 |
| Brand          | -             |
| UBB            | 500571335842  |
| UNSPSC         | 31161504      |
| EAN            | 8715494119191 |
| PKG. of 1000   | Full Box Only |

### Technical Parameters

|                    |                    |
|--------------------|--------------------|
| Diameter           | M1.6               |
| Length             | 8 mm               |
| Class              | 70                 |
| Driving features   | Phillips           |
| Head shape         | Raised cheese head |
| Material           | Stainless steel    |
| Material technical | A2                 |
| Thread             | Metric thread      |

### Standards

|     |       |
|-----|-------|
| DIN | 7985  |
| ISO | ≈7045 |

### Technical Specification

|                         |      |
|-------------------------|------|
| d-D                     | M1.6 |
| Thread length (min.)    | 15   |
| dk (max.)               | 3.2  |
| Full thread if $L \leq$ | 16   |
| k                       | 1.3  |
| L (mm)                  | 8    |
| No. cross recess        | 0    |
| P                       | 0.35 |

### Technical Drawing

