



DIN 603 Fully Threaded Coach Bolt, Stainless Steel A2-70 M12X110

Article number	51501.120.110
Brand	-
UBB	500633260160
UNSPSC	31161612
EAN	8715494594936
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M12
Length	110 mm
Threaded pitch (P)	1.75
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Standards

DIN	≈603
ISO	≈8677

Technical Specification

d-D	M12
dk (max.)	30.65
k (max.)	6.95
L (mm)	110
P	1.75
fn (max.)	8.75
Vn (max.)	12.7

Technical Drawing

