



DIN 603 Fully Threaded Coach Bolt, Stainless Steel A2-70 M12X120

Article number	51501.120.120
Brand	-
UBB	500633260244
UNSPSC	31161612
EAN	8715494594943
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	120 mm
Threaded pitch (P)	1.75
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Standards

ISO	≈8677
DIN	≈603

Technical Specification

d-D	M12
dk (max.)	30.65
k (max.)	6.95
L (mm)	120
P	1.75
fn (max.)	8.75
Vn (max.)	12.7

Technical Drawing

