



## Hexagon domed cap nut, high type DIN 1587 Stainless steel A8 (1.4529) M6

Article number	52400.060.001
Brand	-
UBB	500695123124
UNSPSC	31161705
EAN	8715492003195
PKG. of 20	Full Box Only

### Technical Parameters

Diameter	M6
Driving features	Hexagon
Material	Stainless steel
Material technical	A8 (1.4529)
Thread direction	Right
Thread	Metric thread

Info	<p>HCR (High Corrosion Resistant) alloy</p> <p>1.4529 is a so-called super austenitic stainless steel. It provides particularly good resistance to chloride induced stress corrosion and to local occurrences of corrosion such as pitting or crevice corrosion. This alloy is classified in the highest class CRC V (very strong, EN 1993-1-4) for components and fasteners. Fasteners in 1.4529 are therefore ideal for use in indoor swimming pools and traffic tunnels.</p>
------	---

### Standards

NEN	1618
DIN	1587

Technical Specification

d-D	M6
dk (max.)	9.5
h	12
m (max.)	5
P	1
s	10
t	8

Technical Drawing

