

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Stainless Steel A4-80 M5X25

Article number	53510.050.025
Brand	-
UBB	500571353571
UNSPSC	31161620
EAN	8715494111584
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	25 mm
Class	80
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NEN	1555
NF	E25-112
ASME	B18.2.3.1M
DIN	931
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	22
b (min.): L≤125mm	16
d-D	M5
k	3.5
L (mm)	25
P	0.8
s	8

Technical Drawing

