

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Stainless Steel A4-80 M6X35

Article number	53510.060.035
Brand	-
UBB	950351912122
UNSPSC	31161620
EAN	8715492317803
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	35 mm
Class	80
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NF	E25-112
ISO	4014
DIN	931
ASME	B18.2.3.1M
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	24
b (min.): L≤125mm	18
d-D	M6
k	4
L (mm)	35
P	1
s	10

Technical Drawing

