

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Stainless Steel A4-80 M8X100

Article number	53510.080.100
Brand	-
UBB	950351831447
UNSPSC	31161620
EAN	8715492317964
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M8
Length	100 mm
Class	80
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NF	E25-112
ASME	B18.2.3.1M
DIN	931
NEN	1555
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	100
P	1.25
s	13

Technical Drawing

