

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Stainless Steel A4-80 M10X110

Article number	53510.100.110
Brand	-
UBB	500571356210
UNSPSC	31161620
EAN	8715494111850
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	110 mm
Class	80
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ISO	4014
NEN	1555
DIN	931
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	110
P	1.5

Technical Drawing



